# PS-02 series <pH-conductivity-temperature> Portable pH/Electric conductivity meter pH, conductivity, temperature are **CEMCO** measurable in one meter L M H WATERPROOF PS-02 pH/Electric conductivity/Temperature/ORP/TDS are measurable

- ●High repeatability pH:±0.02pH Conductivity:±2% Temperature:±1°C
- Auto calibration, Hold function
- Switch pH and conductivity in one touch operation
- Record and store the measuring value
- Easy to carry around with the carry case



 Data transfer to the computer is easy with USB port



# pH/Electric conductivity/Temperature/ORP/TDS are measurable. USB port is equipped for sending data.

Model		PS-02-PH	PS-02-PH/EC	
рН	Measuring method	Glass e	lectrode	
	Measuring range	0.00~14.00pH		
	Display range	-2.00∼16.00pH		
	Resolution	0.1/0.01pH		
	Meter repeatability	±0.02pH±1digit		
	Temp.compensation	0~80°C		
ORP	Measuring method	Meatal electrode		
	Measuring range	±1999mV		
	Resolution	0.1mV when ±200mV,1mV when other		
	Accuracy	±2mV,±1digit		
Electric Conductivity	Measuring range	_	0~200mS/cm 0.00~19.99μS/cm 20.0~199.9μS/cm 200~1999μS/cm 2.00~19.99mS/cm 20.0~199.9mS/cm TDS: 0~100g/L, Salt: 0~100ppt	
	Resolution	_	0.01/0.1/1μS, 0.01/0.1mS/cm	
	Meter repeatability	_	±2.0%FS±1digit	
	Temp.compensation	_	0~80℃	
	Cell constant	_	0.1/1/10cm-1	
Temperature	Display range	-10~110℃		
	Resolution	0.1℃		
	Accuracy	±0.5℃±1digit		
Data number can be saved		500 data		
Saved content		Data number,Date,Time,Measured value,Measuring unit,Temp.		
Connection		USB		
Power supply		AA Battery x3		
IP		Equivalent IP57		
Body size and weight		86 x 196 x 33mm, 335g		
Case size and weight		330 x 270 x 82mm, 1.3kg	370 x 270 x 77mm, 1.8kg	
Standard accessory		Main body,electrode,Case	Main body,electrode,Case	
		Driver,pH standard solution(4.00/7.00)	Driver,pH standard solution(4.00/7.00)	
		UCB cable,Manual,CD-ROM —	Conductivity solution(1413µS,12.85mS)  UCB cable,Manual,CD-ROM	
			OCB Cable,Maridat,CD-NOM	

#### PS-02-PH set



#### ●PS-02-PH/EC set







## **Features**

### ■pH and Electric conductivity are measurable in one meter (model PS-02-PH/EC)

 $pH(0\sim14pH)$ , Conductivity  $(0\sim200mS/cm)$ , Temperature  $(0\sim80^{\circ}C)$ , TDS are measurable in one meter. ORP is also measurable by changing the sensor.

#### ■Hold / Auto power off function

Hold function: Lock the measure value for recording Auto power off function: Auto power off when no operation for 10 minutes

### Large display

Large LCD would display pH, Electric conductivity, Temeperature in one screen.

#### 3 points calibration

3 points calibration system is equipped so high accuracy measurement is possible (pH)



## **CEM CORPORATION**

\* Specifications and appearance may change without prior notice due to improvements.

\* The actual color of the products may be slightly different from that shown in the brochure due to issues of color during printing

Head office: 1-10-25 Honkomagome, Bunkyo-ku, Tokyo 1138638 Phone:81-3-3946-3335 Fax:81-3-3946-0675

Overseas sales dept.: 4-45-17, Sengoku, Bunkyo-ku, Tokyo 1120011 Phone:81-3-3946-3201 Fax:81-3-3946-3210

TAIWAN CEMCORPORATION: 3F, No.56, Sec.2, Jhongcheng Rd., Shilin District, Taipei 111, Taiwan

Phone:886-2-2836-8603 Fax:886-2-2832-1148

SHANGHAI CEMCORPORATION: 206 Floor A, 288 Yu Yao Lu Jingan Qu, Shanghai Shi Phone:86-21-6231-7631 Fax:86-21-6230-9736

